

PRODUCT

Static Shielding Bag -Grip Seal

TECHNICAL DATASHEET

DESCRIPTION

These grip seal, easy access static shielding bags are designed to protect sensitive electronic devices against ESD during transit and whilst kept in storage.



1) CONFIGURATION(S)

Our bags are available in custom sizes or in several industry standard sizes. Bags are offered in a 2-seal configuration and bottom fold, with our standard flexographically printed artwork.

Please note, thew standard measurements for grip seal bags are taken from the grip seal to the bottom fold or seal. Any bags that are longer than 24" will have a 3rd seal along the bottom edge.



FEATURES

- Metal "Faraday cage" layer shields products from electric energy inside and prevents static build-up
- Four layer protection guards against charges inside and out
- Semi transparent for easy content identification
- Surface resistance of 10⁶-10¹⁰ Ohms
- Custom sizes and print available on request
- Suitable for packing electronic products which are sensitive to static, eg PCBs, electronic components etc.

2) BAG ARTWORK

Our static shielding bags are produced with the following sample artwork as standard. For further information on bespoke/printed orders, please contact one of our sales team. Please note there is a MOQ of 20,000 bags on all custom printed bags.

To request a quotation or for more information, please call **+44 (0)1473 836200** email **info@antistat.co.uk** or visit **www.antistat.co.uk**


IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of uses or of the products. Antistat assumes are or where Antistat was aware of the possibility of uses or line are arised. Antistat assumes are used to a state the antistat was aware of the possibility of uses or line are arised. Antistat



3) CONSTRUCTION

Our static shielding bags are constructed in four layers, consisting of a static dissipative polyester outer layer and a static dissipative polyethylene inner layer with a centre metallised shield layer. Our bags are manufactured from industry approved polyester and polyethylene laminates. The polyester dielectric works with the metal layer to provide a Faraday effect, the metal layer preventing penetration from damaging electrostatic fields.

The specially processed polyethylene keeps tribocharging to a minimum.



TEST CONDITIONS

Results below were taken under the following environmental test conditions: Temperature: 23°C / Humidity: 12% RH.

ITEM	TEST METHOD	TYPICAL VALUE	
Film thickness	Micron Meter	3Mil 75 micron	
Metal layer optical transmission	ASTM D1003 (TOBIAS)	40% +/- 5% optical density	
Surface resistance	STM 11.11	10 ⁶ -10 ¹⁰ Ohms	
Time for static removal	FTMS 101B Method 4046 - 5000-0V	<.0.03 Sec	
Static shielding - Energy penetration	ESD-STM-11.31 @12% R.H.	<20 nJ	
Static shielding - Capacitive probe	EIA 541 Appendix E	<25V	
Friction static	E1A541 Appendix C Avg.	Triboelectric nanocoulombs Quartz +0.01 Tefion -0.09	
Anti-erosion	FTMS 101C Method 3005	No visible spots	
Tensile strength	ASTM D882-91, Method A	MD 6530 psi TD 5800 psi	
Tear initiation	ASTM D1004 -94-Notched	MD 2.5 lbs./in TD 2.0 lbs	
Puncture resistance	ASTM D3420	>10 psi	
Tear resistance	ASTM D882	>8 psi	
Burst strength	FTMS 101 C Method 2065.1	50 psi nominal	
Heat seal temperature	-	250 - 375 °F	
Heat seal pressure	-	30-70 PSI	
Heat seal strength	(D1876-93) Vertrod bar sealer/heat	>12 lbs/in width (room temperature)	
Breaking elongation rate	ASTM D882-91 Method A	MD 80% TD 85%	
Appearance	-	No delamination, burst seal, wrinkle, warp, break, foreign particle adherence, air bubble beyond sealing ≤3mm	

To request a quotation or for more information, please call +44 (0)1473 836200 email info@antistat.co.uk or visit www.antistat.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themsetwes the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2024 Antistat.



TEST CONDITIONS

The shielding bag is tested accordance with the relevant test standard and requirements.

TEST ITEM	TEST METHOD	MEASURED EQUIPMENT(S)	MDL
Lead (Pb)	IEC 62321:2008 Ed.1 Sec.8	ICP-OES	2mg/kg
Cadmium (Cd)	IEC 62321:2008 Ed.1 Sec.8	ICP-OES	2mg/kg
Mercury (Hg)	IEC 62321:2008 Ed.1 Sec.7	ICP-OES	2mg/kg
Hexavalent Chromium (Cr(VI))	IEC 62321:2008 Ed.1 Annex C	UV-Vis	2mg/kg
Polybrominated Biphenyls (PBBs)	IEC 62321:2008 Ed.1 Annex A	GC-MS	5mg/kg
Polybrominated Diphenyl Ethers (PBDEs)	IEC 62321:2008 Ed.1 Annex A	GC-MS	5mg/kg

PRODUCT CODE	DESCRIPTION	SIZE (inch)	SIZE (mm)	PACK QUANTITY
013-0001	Static Shielding Bag - Grip Seal	3 x 5	76 x 127	100
013-0018	Static Shielding Bag - Grip Seal	3 x 7	76 x 178	100
013-0044	Static Shielding Bag - Grip Seal	3.4 x 5.4	86 x 137	100
013-0002	Static Shielding Bag - Grip Seal	4 × 4	102 x 102	100
013-0003	Static Shielding Bag - Grip Seal	4 x 6	102 x 152	100
013-0301	Static Shielding Bag - Grip Seal	4 x 8	102 x 203	100
013-0022	Static Shielding Bag - Grip Seal	4 × 14	102 x 355	100
013-0052	Static Shielding Bag - Grip Seal	4 x 24	102 x 609	100
013-0004	Static Shielding Bag - Grip Seal	5 x 8	127 x 203	100
013-0012	Static Shielding Bag - Grip Seal	5 x 10	127 x 254	100
013-0020	Static Shielding Bag - Grip Seal	6 x 8	152 x 203	100
013-0005	Static Shielding Bag - Grip Seal	6 x 10	152 x 254	100
013-0303	Static Shielding Bag - Grip Seal	6 x 18	152 x 455	100
013-0306	Static Shielding Bag - Grip Seal	7 x 11	178 x 279	100
013-0026	Static Shielding Bag - Grip Seal	7 x 15	178 x 381	100
013-0006	Static Shielding Bag - Grip Seal	8 x 10	203 x 254	100
013-0007	Static Shielding Bag - Grip Seal	8 x 12	203 x 305	100
013-0019	Static Shielding Bag - Grip Seal	9 x 12	228 x 305	100
013-0047	Static Shielding Bag - Grip Seal	9.8 x 15.75	250 x 400	100
013-0008	Static Shielding Bag - Grip Seal	10 x 12	254 x 305	100

To request a quotation or for more information, please call +44 (0)1473 836200 email info@antistat.co.uk or visit www.antistat.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2024 Antistat.



PRODUCT CODE	DESCRIPTION	SIZE (inch)	SIZE (mm)	PACK QUANTITY
013-0009	Static Shielding Bag - Grip Seal	10 × 14	254 x 355	100
013-0304	Static Shielding Bag - Grip Seal	12 x 12	305 x 305	100
013-0305	Static Shielding Bag - Grip Seal	12 × 14	305 x 355	100
013-0010	Static Shielding Bag - Grip Seal	12 x 16	305 x 406	100
013-0015	Static Shielding Bag - Grip Seal	16 × 18	400 x 455	100
013-0042	Static Shielding Bag - Grip Seal	18 x 24	457 x 610	100

To request a quotation or for more information, please call +44 (0)1473 836200 email info@antistat.co.uk or visit www.antistat.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2024 Antistat.